

<b>Invoice to:</b>	
Name:	
Street:	
Town:	Postal code:
Country:	
Tel:	Fax:
Order date:	
Purchase order:	



<b>Deliver to:</b>	
Name:	
Street:	
Town:	Postal code:
Country:	
Tel:	Fax:
Marked for:	

Fax: +44 (0)845 605 66 89

**Base Price            £11,550**

E-mail: orders@sunmed.co.uk

**Max. user weight: 160 Kg**

<b>Standard Features</b>	<ul style="list-style-type: none"> <li>● C-Me Drive Technology</li> <li>● Sedeo Ergo Biometric Seating System</li> <li>● 180° Anti Shear Backrest</li> <li>● Powered centre mount legrest</li> <li>● Headrest</li> </ul>	<ul style="list-style-type: none"> <li>● R-Net 120Ah Controller</li> <li>● R-Net Advanced Color LCD Joystick</li> <li>● Capsulated Swing away joystick mount</li> <li>● 6 Programmable Smart seat Memory positions</li> <li>● Lapbelt</li> </ul>
<ul style="list-style-type: none"> <li>● Jive M2 Matt Black Chassis</li> <li>● SpiderTrac 2 Suspension</li> <li>● 60Ah Batteries</li> <li>● 6 or 10Kph 4 Pole Motors</li> </ul>		

### SEAT DIMENSION

Effective seat width <sup>(1)</sup>

cm	40	42	44	46	48	50	52	54	56
<b>40 (4)</b>	○	○	○	○					
<b>42 (4)</b>	○	○	○	○					
<b>44 (5)</b>	○	○	○	○					
<b>Seat depth</b>	<b>46</b>	○	○	○	○	○	○		
	<b>48</b>	○	○	○	○	○	○		
	<b>50</b>			○	○	○	○	○	○
	<b>52</b>					○	○	○	○
	<b>54</b>						○	○	○
	<b>56</b>							○	○

(2)

The seat width can be adjusted between 40 and 56 cm via the seat plate and the armrests.

The seat depth can be adjusted between 40 and 56 cm via backrest movement

**Note: At 40cm seat depth Backrest fully reclines does not lie flat. Stops at 160°**

### SEAT HEIGHT

Seat height (cm)				
Seat to base interface	41	43.5	46	48.5
Filler module	○	○	○	○
50° Power tilt		○ (3)	○ (3)	○
-5° to 45° Powered tilt option				○
Power seat lift and tilt combined			○	○

Seat height measured floor to seat pan at 0° tilt

(1) Physical cushion width = always 4 cm smaller than effective seat width

(2) Not available with 50° tilt module

(3) Not available with 50, 52 and 54cm seat depth

(4) Maximum recline angle 160°

(5) Maximum recline angle 170°

**SEAT TO BASE INTERFACE**

JMV130001	<input type="radio"/>	Filler module			(tool adjustable seat angle)	
		JMV130100 <input type="radio"/> 0°	JMV130106 <input type="radio"/> 6°			
		JMV130103 <input type="radio"/> 3°	JMV130109 <input type="radio"/> 9°			

**Power seating modules (with positioning feedback)**

JMV130007	<input type="checkbox"/>	50° Power tilt (1)	(0° to 50°, with centre of gravity shift)	715
JMV130005	<input type="checkbox"/>	-5° to 45° Powered tilt option	(3 cm added seat to floor height at 0°)	765
JMV130006	<input type="checkbox"/>	Power seat lift and tilt combined	(50° tilt and 30 cm lift)	1760

**SEDEO ERGO SEAT CUSHION OPTIONS**

JMV020501	<input type="radio"/>	Cushion - Air flow upholstery (1)	(Standard option if nothing selected)	
JMV020502	<input type="checkbox"/>	Cushion - Air flow upholstery with incontinence protection (1)		105
JMV020509	<input type="radio"/>	Centre, side cushion and hip support	(Standard option if nothing selected)	
JMV020510	<input type="checkbox"/>	Omit center cushion - Select if JAY cushion required WITH Sedeo Ergo Side supports		-55
JMV020512	<input type="checkbox"/>	Omit center, side cushion and hip support		-110
JMV020513	<input type="checkbox"/>	JAY Cushion - select if JAY Cushion required		-110

		Left	Right			
<input type="checkbox"/>	Lateral s/a knee support	JMV020341	<input type="radio"/>	<input type="radio"/>	JMV020342	160 each
<input type="checkbox"/>	Lateral Thigh Support (2)	JMV020343	<input type="radio"/>	<input type="radio"/>	JMV020344	160 each

**SEDEO ERGO BACK CUSHION OPTION**

<b>Back cushion height</b>	BH51 <input type="radio"/> 51cm	BH56 <input type="radio"/> 56cm	BH61 <input type="radio"/> 61cm	
JMV030051	<input type="radio"/>	Back Upholstery - AIR FLOW		
JMV030209	<input type="radio"/>	Omit back upholstery		

**SEDEO ERGO BACK CUSHION WIDTH**

BW40 <input type="radio"/> 40 cm	BW46 <input type="radio"/> 46 cm	BW52 <input type="radio"/> 52 cm	
BW42 <input type="radio"/> 42 cm	BW48 <input type="radio"/> 48 cm	BW54 <input type="radio"/> 54 cm	
BW44 <input type="radio"/> 44 cm	BW50 <input type="radio"/> 50 cm	BW56 <input type="radio"/> 56 cm	

**POSITIONING STRAPS**

(anterior pelvic supports)

JMV090047	<input type="radio"/>	5 cm aircraft buckle (130 cm length)	
JMV090056	<input type="radio"/>	5 cm aircraft buckle (190 cm length)	
JMV090048	<input type="checkbox"/>	5 cm padded aircraft buckle	55

**SEDEO ERGO HEADRESTS**

JMV030406	<input type="radio"/>	Sedeo Ergo contoured headrest with air flow upholstery (20 x 11 cm)	
JMV030407	<input type="radio"/>	Sedeo Ergo contoured headrest with air flow upholstery (23 x 11 cm)	
JMV030408	<input type="checkbox"/>	Sedeo Ergo flexible comfort headrest with adjustable side wings	105
JMV030415	<input type="checkbox"/>	Omit Headrest	-55

**BACKREST RECLINE OPTIONS**

JMV030034	<input checked="" type="radio"/>	85° to 175° Power recline c/w mechanical shear reduction (3)	
JMV030201	<input type="checkbox"/>	Push Handles	138

(1) please use the cushion composition

(2) Only available with JMV020512; Omit center, side cushion and hip support

(3) Max. 160° at 40 and 42cm seat depth, Max. 170° with 44cm seat depth

## JAY CUSHIONS

For Jay cushion must select omit centre, side cushion and hip support- JMV020512

		Seat Width						
		40	42	44	46	48	50	56
Seat Depth	40	○	○	○	○ <sup>(1)</sup>	○ <sup>(1)</sup>		
	42	○	○	○	○	○		
	44	○	○	○	○	○		
	46	○	○	○	○	○	○	○ <sup>(3)</sup>
	48		○ <sup>(2)</sup>	○ <sup>(2)</sup>	○ <sup>(2)</sup>	○ <sup>(2)</sup>	○ <sup>(2)</sup>	○ <sup>(2/3)</sup>
	50			○ <sup>(2)</sup>	○	○	○	○ <sup>(3)</sup>
	56							○ <sup>(3)</sup>





(1) Not available with Soft Combi P, Easy Fluid & Easy Visco

(2) Only available for Jay Balance cushions

(3) Not available with Jay Lite cushions

JAY020003	<input type="checkbox"/> Jay Soft Combi P	(Incontinence cover)	77
JAY020004	<input type="checkbox"/> JAY Lite Standard version	(Microclimatic cover)	215
JAY020001	<input type="checkbox"/> Jay Easy Visco with Flat Base	(Incontinence cover)	132
JAY020005	<input type="checkbox"/> Jay Easy Fluid with Flat Base	(Incontinence cover)	308
JAY020010	<input type="checkbox"/> Jay Balance Roho (Air Single Valve )	(Microclimatic cover)	495
JAY020011	<input type="checkbox"/> Jay Balance Fluid	(Microclimatic cover)	468

## JAY J3 BACKS - measurements in cm

	5 cm	8 cm	15 cm	15 cm	
					
	Shallow Contour (SC)	Mid Contour (MC)	Deep Contour (DC)	Posterior Deep Contour (PDC)	
<b>Jay J3 Back Size</b>	41   46   51	41   46   51	41   46   51	41   46   51	
<b>Backrest Height</b>	572			572	
Mid Thoracic (MT)	Short (S) - 30	○	○	○	○
	Med. (M) - 34	○	○	○	○
	Tall (T) - 38	○	○	○	○
<b>Backrest Height</b>	572			572	
Upper Thoracic (UT)	Short (S) - 42	○	○	○	○
	Med. (M) - 46	○	○	○	○
	Tall (T) - 50	○	○	○	○
<b>Backrest Height</b>	572			627	
Shoulder Height (SH)	Short (S) - 53	○	○	○	○
	Med. (M) - 57	○	○	○	○
	Tall (T) - 61	○	○	○	○

JAY J3 Back Item Nr. construction: J3 SC MT S 41 (This is only an example)

J3: J3 Back

SC: Shallow Contour

MT: Mid Thoracic

S: Short (Height cm)


41: Chair Backrest Width (cm)

JAY J3 BACK MOUNTING HARDWARE				£																																																								
JAY090065	<input type="checkbox"/>	Jay 3 Back Shell Adaptor																																																										
<b>JAY J3 BACK HEADREST</b> (only available where headrest is indicated on the first page)				<b>Crash tested</b>																																																								
<b>Please choose 1 mount and 1 pad to have a complete headrest with pad</b>				<b>Unit Price</b>																																																								
<b>Mount</b>																																																												
JAY090006	<input type="checkbox"/>	Jay Standard Headrest	(Bracket & Mount only)	88																																																								
JAY090007	<input type="checkbox"/>	Jay Flip Back Headrest	(Bracket & Mount only)	198																																																								
<b>Pad</b>																																																												
JAY090008	<input type="checkbox"/>	Jay Standard Pad		41																																																								
JAY090009	<input type="checkbox"/>	Jay Contour Pad		41																																																								
JAY090010	<input type="checkbox"/>	Universal Headrest Mount	(required to use any other headrest not listed in this order form)	41																																																								
<b>JAY J3 BACK LATERAL SUPPORT</b> (only available where laterals are indicated on the first page)				<b>Unit Price</b>																																																								
<table border="0"> <tr> <td colspan="2"><b>Left Hand lateral</b></td> <td colspan="3">Depth</td> <td></td> </tr> <tr> <td></td> <td>cm</td> <td>10</td> <td>12</td> <td>15</td> <td></td> </tr> <tr> <td rowspan="3">Height</td> <td>10</td> <td><input type="checkbox"/> JAY090011</td> <td><input type="checkbox"/> JAY090012</td> <td><input type="checkbox"/> JAY090013</td> <td>← Fix lateral JAY090017</td> </tr> <tr> <td>15</td> <td><input type="checkbox"/> JAY090014</td> <td><input type="checkbox"/> JAY090015</td> <td><input type="checkbox"/> JAY090016</td> <td>← Fix lateral JAY090018</td> </tr> <tr> <td></td> <td><input type="checkbox"/> JAY090019</td> <td colspan="3">← Swing Away option</td> </tr> <tr> <td colspan="2"><b>Right Hand lateral</b></td> <td colspan="3">Depth</td> <td></td> </tr> <tr> <td></td> <td>cm</td> <td>10</td> <td>12</td> <td>15</td> <td></td> </tr> <tr> <td rowspan="3">Height</td> <td>10</td> <td><input type="checkbox"/> JAY090020</td> <td><input type="checkbox"/> JAY090021</td> <td><input type="checkbox"/> JAY090022</td> <td>← Fix lateral JAY090026</td> </tr> <tr> <td>15</td> <td><input type="checkbox"/> JAY090023</td> <td><input type="checkbox"/> JAY090024</td> <td><input type="checkbox"/> JAY090025</td> <td>← Fix lateral JAY090027</td> </tr> <tr> <td></td> <td><input type="checkbox"/> JAY090028</td> <td colspan="3">← Swing Away option</td> </tr> </table>					<b>Left Hand lateral</b>		Depth					cm	10	12	15		Height	10	<input type="checkbox"/> JAY090011	<input type="checkbox"/> JAY090012	<input type="checkbox"/> JAY090013	← Fix lateral JAY090017	15	<input type="checkbox"/> JAY090014	<input type="checkbox"/> JAY090015	<input type="checkbox"/> JAY090016	← Fix lateral JAY090018		<input type="checkbox"/> JAY090019	← Swing Away option			<b>Right Hand lateral</b>		Depth					cm	10	12	15		Height	10	<input type="checkbox"/> JAY090020	<input type="checkbox"/> JAY090021	<input type="checkbox"/> JAY090022	← Fix lateral JAY090026	15	<input type="checkbox"/> JAY090023	<input type="checkbox"/> JAY090024	<input type="checkbox"/> JAY090025	← Fix lateral JAY090027		<input type="checkbox"/> JAY090028	← Swing Away option		
<b>Left Hand lateral</b>		Depth																																																										
	cm	10	12	15																																																								
Height	10	<input type="checkbox"/> JAY090011	<input type="checkbox"/> JAY090012	<input type="checkbox"/> JAY090013	← Fix lateral JAY090017																																																							
	15	<input type="checkbox"/> JAY090014	<input type="checkbox"/> JAY090015	<input type="checkbox"/> JAY090016	← Fix lateral JAY090018																																																							
		<input type="checkbox"/> JAY090019	← Swing Away option																																																									
<b>Right Hand lateral</b>		Depth																																																										
	cm	10	12	15																																																								
Height	10	<input type="checkbox"/> JAY090020	<input type="checkbox"/> JAY090021	<input type="checkbox"/> JAY090022	← Fix lateral JAY090026																																																							
	15	<input type="checkbox"/> JAY090023	<input type="checkbox"/> JAY090024	<input type="checkbox"/> JAY090025	← Fix lateral JAY090027																																																							
		<input type="checkbox"/> JAY090028	← Swing Away option																																																									
				46																																																								
				46																																																								
				87																																																								
				46																																																								
				46																																																								
				87																																																								
When ordering 2 laterals Left and Right, you need to pick the sizes in both matrices above.				<b>Total Price</b>																																																								
If a swing-away lateral is required, first select the height and the depth, then tick the Swing Away option box below the matrix																																																												
<b>JAY J3 BACK POSITIONING KIT</b>																																																												
				<b>CM width</b>																																																								
				41 cm																																																								
				46 cm																																																								
				51 cm																																																								
				<b>Unit Price</b>																																																								
Spine Align Mini Fit Kit I				<input type="checkbox"/>																																																								
Spine Align Mini Fit Kit II				<input type="checkbox"/>																																																								
JAY090035	<input type="checkbox"/>	Jay 3 Back Positioning Box		151																																																								
JAY090036	<input type="checkbox"/>	Jay 3 Back Hardware Box		474																																																								
<b>JAY J3 BACK CHEST STRAP</b>																																																												
				<b>Medium</b>																																																								
				<b>Large</b>																																																								
				<b>Extra large</b>																																																								
				<b>Unit Price</b>																																																								
Padded Anterior Strap				<input type="checkbox"/>																																																								
				JAY090037																																																								
				JAY090038																																																								
				JAY090039																																																								
Centre open harness (4 point strap, not available with Jay Comfort)				<input type="checkbox"/>																																																								
				JAY090040																																																								
				JAY090041																																																								
				JAY090042																																																								
<b>JAY J3 BACK SPARES</b> (separate to product - separate box or delivery)																																																												
				<b>CM width</b>																																																								
				41 cm																																																								
				46 cm																																																								
				51 cm																																																								
				<b>Unit Price</b>																																																								
Small Lumbar <small>(1 unit included as std with product LT, MT, UT &amp; SH)</small>				<input type="checkbox"/>																																																								
Large Lumbar Support <small>(1 unit included as std with product MT, UT &amp; SH)</small>				<input type="checkbox"/>																																																								
Wedge				<input type="checkbox"/>																																																								
				<b>Unit price</b>																																																								
				<b>Quantity</b>																																																								
				<b>Total Price</b>																																																								
JAY090052	<input type="checkbox"/>	Curved Shim		9																																																								
JAY090053	<input type="checkbox"/>	Flat Shim		9																																																								
JAY090054	<input type="checkbox"/>	Posterior/Lateral Pelvic		12																																																								
JAY090055	<input type="checkbox"/>	Lateral Shim		4																																																								
JAY090056	<input type="checkbox"/>	Small Bean Bag		9																																																								
JAY090057	<input type="checkbox"/>	Large Bean Bag		9																																																								


										£	
<b>ARMREST TYPE</b>										(pair)	
JMV040123	●	Reclining and flip up armrest							(reclining and flip-back)		
JMV040142	□	Fixed Sideguard with Upholstery (1)							(width and height adjustable via seat plate)		165
<b>ARMPADS - LEFT &amp; RIGHT HAND SIDE</b>											
<b>Standard armpads (Microclimatic cover to match Ergo Upholstery)</b>										Left	Right
Comfort armpads		41 cm	JMV040217	○	○	JMV040218					
<b>Comfort armpads</b>											
Skai (vinyl) upholstery		full length	40 cm	JMV040203	□	□	JMV040204		52 each		
P-Shaped skai upholstery		full length	45 cm	JMV040205	□	□	JMV040206		52 each		
<b>Hemi Arm pads</b>											
Hemi forearmpad		small	23 cm (2)	JMV040207	□	□	JMV040208		87 each		
Hemi forearmpad		medium	28 cm (2)	JMV040209	□	□	JMV040210		87 each		
Hemi forearmpad		large	33 cm (2)	JMV040219	□	□	JMV040220		87 each		
<b>Hemi hand pads (required when forearm pad selected)</b>											
Flat hand pads		small	11 x 18 cm	JMV040211	□	□	JMV040212		87 each		
Flat hand pads		large	14 x 23 cm	JMV040213	□	□	JMV040214		87 each		
<b>LEGRESTS</b>											
JMV050111	●	Powered centre mount legrest							Lower leg length 34 cm - 52 cm		
JMV050038	○	Adjustable calf pads with vent air cover									
<b>R-NET CONTROLS / ELECTRONICS</b>											
JMV110004	●	R-NET Heavy Duty motor control (120 A)							(no on board actuator control output)		
JMV110009	□	R-NET Traction Control System (GYRO Control System)								275	
JMV110013	●	Advanced Colour LCD JSM							(with 2 jack inputs, actuator and L&I control)		
JMV110021	□	Dual control (Must also select push handles)							(Separate Dual control module mounted at rear on RH mounted)		438
JMV110020	□	R-Net JSM control ATTENDANT ONLY							(Select JSM above to be used RH mounted)		105
Dual/Attendant control options mounting position				Left	Right						
				○	○	JMV110057					
<b>R-NET CONTROL MOUNTINGS</b>											
<b>Front control mountings</b>										(for single Joystick selection mount)	
JMV110056	●	Capsulated Swing away									
JMV110143	□	Centre tray mounted LCD remote control - Supplied with R-Net Std LCD Joystick (NOT Advanced Joystick)								1606	
				Left	Right						
				○	○	JMV110052					
<b>Actuator Switch Boxes (Comes Standard with USB charger Port)</b>											
JMV110175	□	5-Switch Box with push buttons with free assignable functions								550	
JMV110176	□	5-Switch Box with Toggle Switches with free assignable functions								660	
<b>5-Switch Box mounting position</b>				Left	Right						
				○	○	JMV110077					
<b>LIGHTS &amp; INDICATORS</b>											
JMV110201	●	LED with StVZO approval									
<b>(1) Only available with JMV020512; Omit centre, side cushion and hip support</b>											
<b>(2) Must also select flat hand pad</b>											

						£		
<b>R-NET OPTIONAL CONTROLS / ELECTRONICS</b>								
JMV110031	●	R-NET ISM-L (lighting module)						
JMV110033	●	R-NET CxSM (8-channel seating module) <i>(includes memory seat programming)</i>						
JMV090068	□	R-NET BLUETOOTH MODULE (Controls 1 x Android and Windows device)				215		
JMV090141	□	2nd R-NET BLUETOOTH MODULE (Controls second Android and Windows device)				215		
JMV090142	□	R-NET BLUETOOTH MODULE IOS (Controls Apple Device) <i>(Not available with 2nd Android Bluetooth module)</i>				215		
<b>OMNI DISPLAY &amp; SC INPUT MODULE</b> <span style="float: right;"><i>with IR functionality</i></span>								
JMV110101	□	R-NET OMNI colour display input module <i>(includes Special Control Interface)</i>				876		
JMV110110	○	Flex front control mountings <i>(If JSM selected always mounted opposite to remote pod)</i> <i>(30 cm long flexible height extension)</i>						
			Left	Right				
		JMV110121	○	○	JMV110122			
<b>R-NET SPECIAL HAND CONTROLS</b> <span style="float: right;"><i>R-NET OMNI required; 2 buddy buttons recommended</i></span>								
JMV110102	□	OMNI in scanning mode <i>(c/w 10 assignable functions through DB9 interface)</i>				876		
JMV110130	□	Switch-It Compact Joystick (Versa Guide) as hand control				1693		
JMV110131	□	Switch-It mini joystick as hand control <i>(only fixed mounted)</i>				2276		
JMV110132	□	Switch-It 0-way joystick as hand control <i>(only fixed mounted)</i>				2509		
<b>Mounting options for hand controls</b>								
JMV110150	○	Fixed, front mount		Left	Right			
			JMV110162	○	○	JMV110161		
JMV110151	○	Swing away, front mount		Left	Right			
			JMV110162	○	○	JMV110161		
<b>R-NET HEAD RELATED SPECIAL INPUT DEVICES</b>								
JMV110133	□	Switch-It proximity head array / adult <i>(OMNI required, 2 BB recommended)</i>				3443		
JMV110146	□	Dual Pro Switch-It proportional proximity head control <i>(OMNI required, 2 BB recommended)</i>				4345		
JMV110134	□	Switch-It 0-way joystick as chin control <i>(OMNI required, 2 BB recommended)</i>				2509		
JMV110135	□	Proportional chin control <i>(proportional joystick; OMNI required; 2 BB recommended)</i>				876		
JMV110136	□	Sip & Puff control <i>(tube and mouthpiece; OMNI required; 2 BB recommended)</i>				293		
JMV110137	□	Switch-It mini joystick as chin control <i>(OMNI required, 2 BB recommended)</i>				2276		
JMV110138	□	Switch-It proportional head control <i>(OMNI required, 2 BB recommended)</i>				3210		
JMV110139	□	Switch-It Compact Joystick (Versa Guide) as chin control <i>(OMNI required, switch kit incl.)</i>				1810		
<b>Mounting options for head and chin controls</b>								
JMV110152	□	Manual s/a option		Left	Right	228		
			JMV110162	○	○	JMV110161		
JMV110153	□	Powered s/a option operated with PIKO button <i>(operated via one Piko button; only RH mounted)</i>				1693		
<b>PIKO BUTTON SWITCHES</b> <span style="float: right;"><i>per switch</i></span>								
JMV110191	□	Red	x 1	JMV110192	□	Red	x 2	87 each
JMV110193	□	Green	x 1	JMV110194	□	Green	x 2	87 each
JMV110195	□	Yellow	x 1	JMV110196	□	Yellow	x 2	87 each
JMV110197	□	Blue	x 1	JMV110198	□	Blue	x 2	87 each


<b>MID WHEEL DRIVE POSITION</b>		
JMV080310	● JIVE M2 always with 6" solid castor wheel on front and rear	
<b>SPEED</b>		
JMV180005	<input type="radio"/> 6 kph (4 - pole)	
JMV180007	<input type="radio"/> 10 kph (4 - pole)	
JMV180008	<input type="checkbox"/> 13 kph (4 - pole) <i>(High Speed Low torque - Not recommended for obstacle climbing)</i>	358
<b>DRIVE WHEELS - Tyres and rims always black with coloured inserts</b>		
JMV070051	<input type="radio"/> 14" Pneumatic "V-type" <i>(without coloured insert at the wheel)</i>	
JMV070050	<input type="radio"/> 14" Solid "V-type"	
JMV070053	<input type="radio"/> 14" Pneumatic "knobby"	
JMV070052	<input type="radio"/> 14" Solid "Knobby"	
<b>SUSPENSION</b>		
JMV010901	<input type="radio"/> Performance Spring Sports suspension, <i>(Greater traction &amp; more responsive ride. Reduced kerb climbing to 7cm max)</i>	
<b>BATTERIES</b>		
JMV160001	<input type="radio"/> 60 Ah maintenance free <i>(pair)</i>	
JMV160005	<input type="checkbox"/> 80 Ah maintenance free <i>(pair)</i>	111
<b>CHARGER</b>		
JMV160100	<input type="radio"/> 220V/ 8A automatic charger (UK)	
JMV160103	<input type="checkbox"/> 220V/ 10A automatic charger (UK) <i>(required for 13 kph speed option)</i>	168
<b>SEAT SHROUD INSERT COLOURS - frame and chassis body is always matt black</b>		
JMV140001	<input type="radio"/> White <i>(Colour RAL Code: 9010)</i>	
JMV140005	<input type="radio"/> Apple Green <i>(Colour RAL Code: 110 70 77)</i>	
JMV140003	<input type="radio"/> Blue <i>(Colour RAL Code: 260 40 45)</i>	
JMV140004	<input type="radio"/> Black (20% Gloss) <i>(Colour RAL Code: 9005)</i>	
JMV140006	<input type="radio"/> Orange <i>(Colour RAL Code: 060 60 80)</i>	
JMV140002	<input type="radio"/> Red <i>(Colour RAL Code: 040 40 67)</i>	
<b>ACCESSORIES</b>		
JMV090067	<input type="radio"/> Rear view mirror	
JMV090061	<input type="checkbox"/> 24/12V DC/ DC converter	228
JMV090505	<input type="checkbox"/> Golf ball joystick knob	33
JMV090506	<input type="checkbox"/> T-bar B38 joystick knob	33
JMV090507	<input type="checkbox"/> Soft ball joystick knob	33
JMV090508	<input type="checkbox"/> Ball joystick knob	33
JMV090509	<input type="checkbox"/> Chin cup joystick knob	33
JMV090510	<input type="checkbox"/> Stick joystick knob	33
JMV090511	<input type="checkbox"/> Mushroom joystick knob	33
JMV090512	<input type="checkbox"/> Swing-away tray table	171
JMV090069	<input type="checkbox"/> Bluetooth USB mouse receiver	105
<b>Quickie Jive M2 SEDEO ERGO</b>		<b>£11,550</b>
Option Price		£
<b>Total Price</b>		<b>£</b>




General




Example: eff. seat width 460 mm




Example: Min. seat width 400 mm



General



Example: eff. seat width 460 mm



Example: Min. seat width 400 mm





JAY090006



JAY090007



JAY090008



JAY090009



Fixed laterals



Swing-away laterals



JAY090029 - JAY090031



JAY090032 - JAY090034



JAY090035



JAY090036



JAY090037 - JAY090039



JAY090040 - JAY090042



JAY090043 - JAY090045



JAY090046 - JAY090048



JAY090049 - JAY090051



JAY090052














JAY090053



JAY090054



JAY090055

 <p>JMV130007</p>	 <p>JMV130006</p>	 <p>JMV030051</p>	 <p>JMV030406 &amp; JMV030407</p>
 <p>JMV020509</p>	 <p>JMV020510</p>	 <p>JMV020341 &amp; JMV020342</p>	 <p>JMV020512</p>
 <p>JMV030034</p>	 <p>JMV050111</p>		
 <p>JMV040123</p>	 <p>JMV040217 &amp; JMV040218</p>	 <p>JMV040203 &amp; JMV040204</p>	 <p>JMV040205 &amp; JMV040206</p>
 <p>JUP040207 - .210 &amp; .219 - .220</p>	 <p>JUP040211 / .212 / .213 / .214</p>	 <p>JMV110013</p>	 <p>JMV110056</p>
 <p>JMV110175</p>	 <p>JMV110176</p>	 <p>JMV110101</p>	



JMV110201



JMV110130



JMV110191 - JMV110198



JMV110133



JMV110146



JMV110132



JMV110138




JMV110139



Knobby



V-Type



JMV090067



JMV090061



JMV090505



JMV090506



JMV090507



JMV090508



JMV090509



JMV090510



JMV090511



**Dealer Assessment & handover Set up Notes**  
**NOT FOR ORDERS USE**



**BIOMETRIC SMART SEATING - MEMORY FUNCTIONS**

Memory Function	Default Setting	Customer Requirement
1	Seated	
2	Lie Down	
3	Pressure Relief	
4	Relax	
5	Blank	
6	Blank	

--

**PRESSURE RELIEF COACHING FUNCTION**

<b>Interval reminder</b>	
--------------------------	--

<b>Duration for pressure relief</b>	
-------------------------------------	--

--

**BIOMETRIC REPOSITIONING**

<b>Factory Setting: ON</b>	<b>Customer Requirement</b>	<input type="checkbox"/> <b>YES</b>	<input type="checkbox"/> <b>NO</b>
----------------------------	-----------------------------	-------------------------------------	------------------------------------

ASSIGNABLE BUTTONS - EXMAPLE OF FUNCTIONS TO ASSIGN

Seating	Memory Functions	Latched Functions (Moves automatically)	Connectivity
Tilt Forward	Lie Flat	Tilt - Latched	InfraRED - TV ON
Tilt Backward	Transfer Position	Lie Down - Latched	InfraRED - TV OFF
Tilt - Toggle (rotates between forward/back)	Custom Memory Position	Custom Memory Position - Latched	Bluetooth

DEALER NOTES FOR ASSESSMENT TO PROGRAM AT HANDOVER

TOP LEFT BUTTON Factory Setting (1st Function)	
HAZARD ON	
Re-assign 1st Function (short press)	Re-assign 2nd Function (Long press)

TOP RIGHT BUTTON Factory Setting (1st Function)	
LIGHTS ON	
Re-assign 1st Function (short press)	Re-assign 2nd Function (Long press)

BOTTOM LEFT BUTTON Factory Setting (1st Function)	
LEFT INDICATOR	
Re-assign 1st Function (short press)	Re-assign 2nd Function (Long press)

BOTTOM RIGHT BUTTON Factory Setting (1st Function)	
RIGHT INDICATOR	
Re-assign 1st Function (short press)	Re-assign 2nd Function (Long press)

MODE BUTTON Factory Setting (1st Function)	
MODE	
Re-assign 1st Function (short press)	Re-assign 2nd Function (Long press)
<b>DO NOT CHANGE</b>	

TOGGLE UP Factory Setting (1st Function)	
SPEED UP	
Re-assign 1st Function (short press)	Re-assign 2nd Function (Long press)

PROFILE BUTTON Factory Setting (1st Function)	
PROFILE	
Re-assign 1st Function (short press)	Re-assign 2nd Function (Long press)
<b>DO NOT CHANGE</b>	

TOGGLE DOWN Factory Setting (1st Function)	
SPEED DOWN	
Re-assign 1st Function (short press)	Re-assign 2nd Function (Long press)



BUTTON 1	
PUSH FORWARD	PUSH BACK
LIE DOWN	SEATED
REASSIGN FORWARD	REASSIGN BACK



BUTTON 2	
PUSH FORWARD	PUSH BACK
LIFT UP	LIFT DOWN
REASSIGN FORWARD	REASSIGN BACK

BUTTON 3	
PUSH FORWARD	PUSH BACK
TILT BACK	TILT FORWARD
REASSIGN FORWARD	REASSIGN BACK



BUTTON 4	
PUSH FORWARD	PUSH BACK
RECLINE BACK	RECLINE UP
REASSIGN FORWARD	REASSIGN BACK

BUTTON 5	
PUSH FORWARD	PUSH BACK
LEGREST EXTEND UP	LEGREST BACK
REASSIGN FORWARD	REASSIGN BACK



Dealer Assessment & handover Set up Notes  
**NOT FOR ORDERS USE**



JIVE M2 SEDEO ERGO CONNECTIVITY

MODULE	DEVICE TO BE CONNECTED & SET UP
BLUETOOTH - ANDROID 1	
BLUETOOTH - ANDROID 2	
BLUETOOTH - APPLE	
INFRA RED	TV:
	TV2:
	TV3:
	DVD PLAYER:
	SKY BOX:
	STEREO:
	<b>ENVIRONMENTAL PRODUCTS - GEWAH CODES (DOOR OPENING, BLIND OPENERS, INFRA RED CENTRAL HEATING CONTROL, DOOR INTERCOMMS) (Client must have pre existing Infra red devices installed in the home - Rnet advanced can then control these devices)</b>